



More Measuring Volume


ZEISS ProMax E

Probe racks store stylus systems, probes and sensors when they are not in use. They enable the automatic CNC change of these components and thus increase the efficiency of your coordinate measuring machine. ZEISS offers a suitable solution for every challenge.

ZEISS ProMax provides styli systems outside the measuring range. This ensures that the measuring volume for the workpiece and the travel path of the measuring head are ideally used and that collisions are avoided.

Advantages and Characteristics ✓

- Extension for small footprints and therefore more available measuring range
- Up to 27 MT/VAST or XTR stylus systems available
- More safety: improved repeatability by electric drive
- Can be combined with every ZEISS probe socket
- Modular system gives a high degree of variance and the right solution for each requirement
- Extendable by a third storage level



Interested?



Just Grab it Online
zeiss.ly/metrology/shop/en

Carl Zeiss Industrial Metrology, LLC
 6250 Sycamore Lane North
 Maple Grove, MN 55369/USA

Phone: +1 800 327-9735
 Fax: +1 763 533-0219
info.metrology.us@zeiss.com



Seeing beyond