

# Precision meets Acceleration.

ZEISS O-INSPECT Accessories



## Always the right accessories – for every step of your measuring process

Would you like to increase your productivity without compromising on precision? Our original accessories were developed specifically for the ZEISS O-INSPECT to accelerate your productivity.

### Fast and precise preparation




**ZEISS FixAssist XXT** simplifies the precise adjustment of stylus systems.



**ZEISS Stylus Assembly Pliers** shorten preparation time and simplify assembly.



### Fast and efficient set-up



**ZEISS OMEGA Pallets** increase the productivity of the measuring machine and reduce the set-up time.



**ZEISS OmniFix** offers an optimal combination of accessibility and flexibility.



### Independent accuracy checks



**ZEISS Reference Spheres** ensure precise measuring results for all available sensors on a regular basis.




**ZEISS Calibration Artifacts** check and ensure the precision of the CMM.



**ZEISS Temperature Sensors** record the workpiece temperature to ensure accurate measuring results.



### Exact and reliable measurement



**ZEISS Stylus Systems** optimized for the VAST XXT probe - enables precision and flexibility.



**ZEISS Diffusors** for even light distribution to optimize your measurements.



**ZEISS DotScan** can be used flexibly, even for thickness measurements of transparent surfaces.



### Optimal storage



**ZEISS Multi Sensor Racks** accelerate measuring processes via automatic stylus system change.



**ZEISS ProMax** makes optimal use of the available measuring range and prevents collisions.



**ZEISS Multi Sensor Cabinet** organizes parts in the measuring room and protects your stylus systems.



Discover our large selection of original ZEISS accessories – and put your productivity into the fast lane!

SHOP

INFO